

## **TECHNICAL SPEC FOR Rinse/dry system**

---

**System Model:**

**Semitool ST270**

**Specific Model:**

**Wafer size: 6inch**

**Chemicals used: DI water & N2**

**DI Water: yes**

**Motor seal: Ferrofluidic**

**Motor type: Brushless motor**

**N2 Heater: installed**

**Tachometer: installed**

**Resistivity monitoring: installed**

**Rotor type: PFA high profile cassette**

**Controllers: P-328**

**Process applications: rinse & dry, cleaning**

**SECS: not installed**

**Vintage:**

**Missing parts: none**

**Defected parts: semitool11 not working**

**Software: ON chip**

**Operating system:**

## Photos to Collect

---

- All 4 sides
  - Process console
  - Electronic console
  - Canister console
- Control panel
- Inside all cabinets (boards, electronics and chemicals)
- Serial plate
- Spare parts, manuals (if any)